



Lamp, Ultraviolet, Long-Wave 230 Vac, 50 Hz

Product #:

2184302

Contains mercury. Dispose of according to local, state and federal regulations.

USD Price:
Available

Contact Hach

Mid-size UV lamp (6 Watt) high intensity, hand-held and line-operated. Intensity at 15.2 cm (6"), 750 $\mu\text{W}/\text{cm}^2$. Filters: Two 6 x 7.6 cm (2.4 x 3") in snap on/off frame. Overall dimensions: 37.5 x 8.9 x 6.7 cm (14.8 x 3.5 x 2.6"). Weight: 0.91 kg (2 lbs). UL listed. Meets existing OSHA electrical standards. 365 nm. UV Products.

Note: Users in the European Union- plug not included.

Specifications

Quantity: 1