



Refractometer, Automotive

Product #: 2300055
USD Price: Contact Hach
Ships within 2 weeks

Ideal for measuring refractive index in automotive solutions including anti-freeze and battery acid. The measurement can be displayed as Propylene glycol 32 to -50°F, Ethylene glycol 32 to -50°F, Battery acid 1.000-1.500 sg or Cleaner 14-40.

Small, light weight and as simple to use as a basic optical refractometer, but with the accuracy of a digital readout. Sample size can be as small as 1mL. The temperature is initially displayed followed by the measurement results.

The sophisticated microprocessor provides automatic calibration, automatic temperature compensation and automatic shutoff (after 3 minutes). A sturdy soft-sided water resistant case protects the electronics from wet environments and makes for easy clean ups. Features one button calibration to distilled water and indicates when the battery should be replaced (8000 readings).

Portable

Portable refractometer is small enough to hold in the palm of your hand.

Accurate

Reliable and accurate results in the field.

Digital display

Easy to read LCD display shows measurement results.

Sturdy

Hard plastic housing and soft, water resistant case protects the refractometer from wet environments and makes for easy cleaning.

Battery operated

Easy to replace, requires 1 AAA (1.5V) battery.

Specifications

Accuracy 2:	± 2.0 °F
Measurement Method:	Automotive
Range 2:	Glycol: 32 to -50 °F
Resolution:	0.1 °F
Weight:	0.15 kg

What's in the box?

Comes ready to use with distilled water, transfer-pipet, AAA battery, instructions and a carrying case.