

Membrana de nylon, hidrófila; 0,45 µm, 47 mm, blanca, superficie lisa

Descripción	
Número de catálogo	HNWP04700
Descripción	Membrana de nylon, hidrófila; 0,45 µm, 47 mm, blanca, superficie lisa
Información preliminar	Nylon filters are compatible with a broad range of solvents. Two types are available: 1) Nylon Membrane Filters with pore sizes ranging from 0.20 to 1.2 µm, and 2) Woven Net Filters with mesh openings ranging from 5 to 180 µm. Our 5 µm Nylon Woven Net Filter (NY054700) is commonly used in the automotive industry for cleanliness analysis. Features & Benefits: •Wide range of pore sizes available •Resistant to aggressive solvents Applications: Particle Removal and Clarification; Solvent Filtration; Particle Analysis; Paint Monitoring; Automotive Cleanliness Analysis
Información del producto	
Código del filtro	HNWP
Color del filtro	Blanco
Tipo de filtro	Filtro de membrana
Aplicaciones	
Aplicación	0.45 um pore size, hydrophilic nylon membrane, 47 mm diameter

Información biológica	
Humectabilidad	Hidrófila
Información fisicoquímica	
Tamaño de poro	0.45 µm
Punto de burbuja a 23 °C	≥2,5 bar
Dimensiones	
Superficie del filtro	Lisa
Grosor	170 µm
Diámetro del filtro (ø)	47 mm
Información de materiales	
Química	Nylon
Información sobre embalaje	
Cantidad	100