

Previously known as: Hylite™



Oil



Medium Duty

## Fully dipped nitrile-coated gloves, offering a sturdy alternative to light leather, cotton or PVC gloves

- **Assured protection:** ActivArm® 47-402 work gloves feature a fully dipped nitrile coating, delivering mechanical protection, oil repellency, abrasion resistance and flexibility
- **Enhanced durability:** Thanks to this hard-wearing nitrile coating, these industrial gloves outwear PVC-coated alternatives by a margin of 3 to 1, light leather by 5 to 1 and cotton by 12 to 1
- **Elevated comfort:** An interlock knit lining and range of available sizes mean these medium-duty nitrile-coated gloves offer truly comfortable hand protection
- **Optimized usability:** Their ergonomic design is shaped to natural hand contours, for ease of use over long, sustained periods of time
- **Reduced surface defect risks:** Silicone-free, they maintain the cleanliness of metal sheets they come in contact with, preventing contaminant transfer prior to painting



### Industries

- Automotive
- Machinery and Equipment
- Metal fabrication
- Chemical

### Applications

- Handling metal sheets & panels
- Chassis assembly, body trimming
- Final assembly
- Inspection (picking, checking and marking)
- Cutting glasses, sheets, panels
- Fabricating metal parts, glass sheets
- Assembly & inspection of components
- Warehousing of raw materials
- Loading and unloading trucks and vehicles
- Handling incoming goods

Previously known as: Hylite™

### Key Features

- **Nitrile formulation:** Abrasion resistance, oil repellency and flexibility
- **Interlock knit lining and generous sizing:** High levels of comfort
- **Contoured ergonomic hand shape:** Better for long, sustained wear

### Performance Standards & Regulatory Compliance



### Specifications

| BRAND   STYLE    | DESCRIPTION                                                                                                                                   | Gauge | SIZE        | LENGTH                         | COATING COLOR | PACKAGE                                  |
|------------------|-----------------------------------------------------------------------------------------------------------------------------------------------|-------|-------------|--------------------------------|---------------|------------------------------------------|
| ActivArm® 47-402 | <b>Finishing:</b> Fully Coated<br><b>Coating Material:</b> Nitrile<br><b>Liner Material:</b> Interlock cotton<br><b>Cuff Style:</b> Knitwrist | N/A   | 7, 8, 9, 10 | 265-295 mm; 10.74-11.37 inches | Blue          | • 12 pairs in a bag; 12 bags in a carton |

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 900  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Canada

Ansell Canada  
105 Lauder  
Cowansville, QC J2K 2K8  
Canada  
T: +1 800 363 8340  
F: +1 800 267 3551

#### Australia

Ansell Limited  
Level 3, 678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

#### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jalan Teknokrat 6  
T: +603 8310 6688  
F: +603 8310 6699