



Clack®

WS2EE

WATER
SPECIALIST
CONTROL
VALVE



NSF

Certified to NSF/ANSI/CAN 61 and NSF/ANSI/CAN 372.

- 2" Top mount control valve suited for commercial/industrial applications
- Epoxy coated lead free brass valve body*
- Economical stainless steel optional meter assembly
- Service flow rate of 115 gpm, backwash 80 gpm
- Solid state microprocessor with easy access front panel settings
- Front panel display for time of day, days until next regeneration, volume remaining, current flow rate and total volume used (Totalizer)
- Four methods to initiate regeneration; meter immediate, meter delayed, time clock delayed or pressure differential
- Optional double backwash feature offers optimum regeneration, cleaning ability and efficiency
- Fully adjustable cycle times with 6-cycle control delivers controlled backwash, downflow brining or upflow brining, slow rinse, second backwash, fast rinse, refill and downflow service
- Coin Cell Lithium battery back-up with an 8 hour carry over
- Level VI 15-volt output DC power supply provides safe and easy installation
- Post treated water regenerant refill
- Reliable and proven DC drive
- One piece expanding seal spacer stack assembly
- Linearly reciprocating piston operation



Optional 2" Meter

Water Specialist 2" EE Control Specifications



Inlet/Outlet (1)	2" Female NPT
Cycles	Up to 6
Valve Material	Lead free brass
Regeneration	Downflow

CONTROL VALVE FLOW RATES

Service @15 psi drop (includes meter)	115 gpm
Backwash @ 25 psi drop	80 gpm Cv
Service	29.7 Cv
Backwash	16.0

OPERATING PRESSURES

Minimum/Maximum	20 psi – 125 psi
-----------------------	------------------

OPERATING TEMPERATURES

Minimum/Maximum	40° – 110° F
-----------------------	--------------

METER SPECIFICATIONS

Accuracy	± 5%
Flow Rate Range	1.5 – 150 gpm
Gallon Range	20 – 1,500,000 gallons
Totalizer	1 – 9,999,000 gallons

DIMENSIONS & WEIGHT

Distributor Pilot	
Valve bodies with 2" Female NPT Inlet & Outlet	1.90" OD (1.5" NPS)
Drain Line Connection (drain line adapters not included)	1.5" Female NPT
Brine Line Adapters Included	1" Male NPT elbow, 3/4" x 1" solvent weld elbow and 1/2" OD Poly Tube Compression
Mounting Base	4" - 8 UN
Height From Top Of Tank	8.5"
Shipping Weight With Meter	29 lbs.

ELECTRICAL SPECIFICATIONS

POWER SUPPLY

	<u>U.S.</u>	<u>International</u>
Supply Voltage	100VAC to 120VAC	200VAC to 240VAC
Supply Frequency	50/60 Hz	50/60 Hz
Output Voltage	15VDC	15VDC
Output Current	500 mA	500 mA

TANK APPLICATIONS

Water Softener	12" – 48" diameter
Water Filter (2)	12" – 36" diameter

CYCLES OF OPERATION

	<u>Softener</u>	<u>Filter</u>
Cycle	Range of time in minutes	
1. Backwash 1st (upflow)	1-95	Backwash 1-95
2. Regenerate Draw/Slow Rinse (downflow)	1-180	
3. Backwash 2nd (upflow)	1-95	
4. Fast Rinse (downflow)	1-95	Rinse 1-95
5. Regenerant Refill (in service with treated water)	0.1-99.0 or off	
6. Service (downflow)		

Options: Backwash Filter, Weather Cover

Compatible with the following typical concentrations of regenerants or chemicals: Sodium chloride, potassium chloride, potassium permanganate, sodium bisulfite, chlorine and chloramines

1. See Distributor Pilot

2. Filter tank size calculated @ 10 gpm of backwash per square foot of bed area