



PVC Flow chamber with 3 x 3/4" FNPT bores

Product #: 08313=A=0001
USD Price: Contact Hach
Call for ship date

Flow cell for 3/4 inch NPT conductivity electrodes (8310, 8311, 8312, 8315, 8316, 8317 series). Dimensions: 32 mm x 140 mm (1.25 in x 5.5 in). Can be used up to 60 °C at 2 bar (140 °F at 29 psi), 25 °C at 10 bar (77 °F at 145 psi)

Specifications

Diameter:	32 mm
Length:	140 mm
Material:	PVC
Operating Temperature Range:	0 - 60 °C
Pressure Range:	max. 15 bar at 25 °C
Process Connection:	0.75 " NPT thread for sensor
Sample Input:	0.75 " NPT inner thread
Sample Output:	0.75 " NPT inner thread