



Evita OXY 1100 125um Membrane Cartridge, Single

Product #:	085G0023
USD Price:	Contact Hach
Ships within 2 weeks	

The OXY 1100 Membrane Cartridges come ready to use. Pre-assembled anode, cathode, electrolyte, and membrane in a foil pack. Multiple Ranges: 25 um XY 1100 Membrane Cartridge (0-2 ppm range), 50 um OXY 1100 Membrane Cartridge (standard range), 125 um OXY 1100 Membrane Cartridge (2-50 ppm range)

Simple

Long Life & Convenience

Multiple Ranges

Specifications

Disposal:	OXY 1100 sensor must be disposed as ordinary industrial waste.
Range:	2.0 - 50 mg/L (ppm) recommended value to maintain operating life
Response Time:	110 s
Special Notes:	This sensor is a part of EVITA OXY 4100 and OXY 4150 sensor
Thickness Membrane:	125 µm