



Filter Holder Polypropylene Reusable for 47mm Disc Membranes

Specification

Filter Type	47FH-S
	Filter: Polypropylene (PP)
Material	O-ring: Silicone
Inlet/Outlet	Inlet: 1/4" NPT thread; Outlet: 1/4" NPT threaded male
Membrane Diameter	47 mm
Size	64mm OD x 52.5mm
Effective Filtration Area	13.8 cm ²
Maximum Operating Pressure	0.5MPa @25°C
Pack Size	1/pk

Features

- Polypropylene (PP) material for wide chemical compatibility
- Designed exclusively for membrane filters
- Convenient, quick and efficient assembly

Applications

- Inline sterile sampling of liquid and gas