



H-DMF Disc Filter Holder 47mm/90mm/142mm

Specification

Materials	Body	304/316L
	Exhaust valve/Drain valve	304/316L
	Clamp	>304/316L
	Feet	304/316L
	Sealing ring/Gasket	Silicone, Fluorine, EPDM
Physical Properties	Membrane Diameter	47mm/90mm/142mm
	Import & Export	Quick Fitting
	Exhaust Valve	inner diameter of 4mm, connected to 8mm tubing
	Maximum Operating Temp.	130°C (266°F)
	Maximum Operating Pressure 0.6 Mpa (6.0 bar)	
Sterility	Sterilization Option	SIP/Autoclavable
Package	Pack Size	1/pk

Applications

It is used for in-line impurity removal, degassing and cold sterilization of conventional solutions, including medicine liquid, beverages, alcohol, drinking water, etc.