

Maxisafe 2030i 1.5m inc UV-C

- Maxisafe2030 i incorporates SmartFlow Plus, Dave Plus and Smart UV technologies to offer protection and an ultimate graphical user interface that facilitates operation. Each unit incorporates Wi-Fi and is ready to connect. Our pre-filter system includes a new, improved and simple sealing solution.
- GUI touchscreen interface.
- LED Interior Lighting
- Cloud-compatible data output
- Ergonomic armrests (optional).
- Versatile SmartPort Access
- SmartFlow Plus automatic compensation.
- 316 stainless steel interior.

