

MaxQ2000CO2Plus 3mm Pkg

- Thanks to the orbital agitation achieved by magnetic force, belts no longer need to be replaced
- Small footprint perfect for use in a_{CO2} incubator
- Specially treated mechanical components protect up to 20% of_{CO2} and 95% in wet conditions
- Convenient external control panel with LED display allows for easy adjustments without opening the camera door
- Minimal heat dissipation ensures that conditions in the_{CO2} chamber are not effective
- Stainless steel construction for protection against corrosive_{CO2} gassing conditions
- A wide selection of accessories to suit most applications
- CO2 resistant shaker can be used outside the_{CO2} incubator for maximum value
- External control box for ease of use without interrupting samples
- Comes standard with a 4-20 mA data output port to provide enhanced security and remote monitoring capability

