

TSX CHROMA 30cf 208v/60Hz

- The drive for sample integrity and security
- Designed to safely store chromatography and other lab instrumentation requiring a temperature range of 2°C to 8°C
- Unique V-drive technology is designed to detect usage patterns such as door openings when a higher compressor speed is needed and periods of stability where the compressor runs at a lower speed, saving energy without compromising protection
- Easy to use microprocessor control with interior light, setpoint security and alarms
- Standard door locks provide comfort and assurance
- Two 2 in. (5 cm) side wall access ports with insulated hinged covers for solvent, waste, and other common tubing and hoses used in chromatography applications.
- Hydrocarbon Safety switch protected internal Duplex outlet standard on all models

