

PLEXIGLASS GABLE COVER

Use Thermo Scientific™ accessories for MaxQ™ 7000 Water Bath Stirrers to increase the utility of MaxQ7000 Water Bath Stirrers. Exceptional innovation, reliability, and accuracy make Thermo Scientific MaxQ7000 shakers, platforms, and accessories the optimal job choice for any laboratory.

For use with (application)for temperatures up to 65°C

For use with (equipment)MaxQ 7000

Product TypeTwo-sided Plexiglas™ roof

Unit SizeEach

