

PC Gable Cover - 2LS & 5L GP

- Complement your water baths with a range hood with a two-way cover that accommodates large flasks or concentric ring covers for steam exposure.
- Extractor hoods
- They allow the atmosphere surrounding the sample to be controlled.
- They improve temperature uniformity and reduce energy consumption.
- Polished stainless steel with plastic gas fitting.
- Each bathroom can accommodate 1 large or 2 small hoods.
- Two-sided roofs
- Improved hinged design allows for open lid work and easier lid removal
- Enjoy a higher space to store workshop labware
- Stainless steel and polycarbonate models
- Warranty varies by country, please contact us for more information

